

PRODUCT DESCRIPTION

The PHONICARE PRIMUS UV-C Hearing Aid Dry & Hygiene Station is our smallest, special for hearing aids designed electronic appliance with UV-C light, for hygienic cleansing, drying, care and store all types of hearing aids, RIC, ITE, BTE, Tinnitus maskers, and Ear molds. Phonicare Stellar is a consumer product designed for personal use at home.

MODEL IDENTIFICATION

Model: Phonicare PRIMUS UV-C
Model No: HED350L

PRODUCT SPECIFICATION IDENTIFICATION

- Hygienic cleansing by 10 minutes UV-C light at wavelength of 253,7 nm, UV-C intensity >400 UV-C/cm²
- Drying by convective flow of dry and warm air.
- Drying temperature about 45°C ± 5°C
- Circuit heating with automatic room- and temperature modulation
- Safety interruption to avoid direct UV-C & temperature >70°C
- Touch sensor start button starts 4 hours comfort-drying program
- Hold sensor button >2 seconds within drying phase for manually turn-off
- Automatically turn-off after 4h drying
- All functions are fully processor controlled Model
- Input voltage control < 6V and > 4V
- Operating based on 5V USB via supplied USB power supply or USB 2.0 port

POWER SUPPLY

- Switching power supply (class V) with USB-socket + USB cable 1.0 m Input: 100-240 V, AC 50-60 Hz
- Output: 5 V, DC, 1 A, Adapter EU/UK/US/AUS available

PHYSICAL DIMENSIONS

- | | WEIGHTS |
|--|-----------|
| • Unit: 85mm (L) x 76mm (W) x 53mm (H) | ± 65 gr |
| • Carton unit packing: 110 mm (L) x 85mm (W) x 55mm (H) | ± 295 gr |
| • Inner box 18 units: 270mm (L) X 260MM (W) X 190MM (H) | ± 2,95 kg |
| • 6 x inner box shipping carton: 630mm (L) x 540mm (W) x 310mm (H) | ± 18,7 kg |

SET INCLUDES

- Paper box
- Active-Dry Box | Power supply | USB Cable
- User Manual

Warranty: One year

CERTIFICATES:



WEEE